

Product information

26 27 200

Snipe Nose Side Cutting Pliers (Stork Beak Pliers)

DIN ISO 5745 IEC 60900 DIN EN 60900



⚡ 1000 V   40° ⊖

- Elastic tips: dimensionally stable even when twisted
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges (hardness approx. 61 HRC) for soft, medium-hard and hard wire
- 40° angled jaws
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	26 27 200
EAN	4003773016090
Pliers	chrome plated
Head	chrome plated
Handles	with dipped insulation, VDE-tested
weight	220 g
Dimensions	200 x 65 x 28 mm
Standard	DIN ISO 5745 DIN EN 60900 IEC 60900

Technische Attribute

	Ø 3.2 mm
	Ø 2.2 mm
	9.5 mm
	3.0 mm
	2.5 mm
	23.0 mm
	73.0 mm
	40
Head width	18 mm
Style	2
VDE tested	yes

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	EAC420c044
UNSPSC 13.1	27112134

technical change and errors excepted