

Product information

37 11 125

Flat Nose Pliers

For precision mechanics

DIN ISO 9655

- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding, bending and adjusting
- Tips precision-ground
- Smooth gripping surfaces
- Edges carefully deburred
- Lap joint
- Flat, wide jaws
- High-grade special tool steel, forged, oil-hardened



General

Article No.	37 11 125
EAN	4003773014287
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	79 g
Dimensions	125 x 78 x 12 mm
Standard	DIN ISO 9655

Technische Attribute

Style	1
	7.0 mm
	2.0 mm
	5.5 mm
	27.0 mm
Head width	12.5 mm

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAA004c004
UNSPSC 13.1	27112104

technical change and errors excepted