

Product information

37 43 125

Flat Nose Pliers

For precision mechanics

DIN ISO 9655

- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- For gripping, holding, bending and adjusting
- Tips precision-ground
- Smooth gripping surfaces
- Edges carefully deburred
- Lap joint
- Round, pointed jaws to bend wire loops
- High-grade special tool steel, forged, oil-hardened



General

Article No.	37 43 125
EAN	4003773043652
Pliers	chrome plated
Head	chrome plated
Handles	plastic coated
weight	76 g
Dimensions	125 x 50 x 12 mm
Standard	DIN ISO 9655

Technische Attribute

Style	4
	8.0 mm
	2.0 mm
	1.0 mm
	27.0 mm
Head width	14.5 mm

Classification

eCl@ss 5.1.4	21040301
proficl@ss 6.0	AAA004c004
UNSPSC 13.1	27112104

technical change and errors excepted