

Product information

44 13 J2

Circlip Pliers

For internal circlips in bore holes

DIN 5256 C

- Solid style, forged
- Non-slip, solid tips
- Straight tips
- DIN 5256 C, straight tips
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



General

Article No.	44 13 J2
EAN	4003773042945
Pliers	chrome plated
Head	chrome plated
Handles	plastic coated
weight	143 g
Dimensions	180 x 49 x 48 mm
Standard	DIN 5256 C

Technische Attribute

Style	1
Size of bore	Ø 19 – 60 mm
Tips (diameter)	Ø 1.8 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted