

Product information

44 13 J4

Circlip Pliers

For internal circlips in bore holes

DIN 5256 C

- Solid style, forged
- Non-slip, solid tips
- Straight tips
- DIN 5256 C, straight tips
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



General

Article No.	44 13 J4
EAN	4003773017301
Pliers	chrome plated
Head	chrome plated
Handles	plastic coated
weight	463 g
Dimensions	320 x 55 x 16 mm
Standard	DIN 5256 C

Technische Attribute

Style	1
Size of bore	Ø 85 – 140 mm
Tips (diameter)	Ø 3.2 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted