

Product information

44 23 J11

Circlip Pliers

For internal circlips in bore holes

DIN 5256 D

- Solid style, forged
- Non-slip, solid tips
- Angled tips
- DIN 5256 D; 90° angled tips
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



90°

General

Article No.	44 23 J11
EAN	4003773042969
Pliers	chrome plated
Head	chrome plated
Handles	plastic coated
weight	89 g
Dimensions	130 x 50 x 12 mm
Standard	DIN 5256 D

Technische Attribute

Style	2
Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted