

Product information

46 31 A12

Circlip Pliers

For external circlips on shafts
45° bent

- Solid style, forged
- Non-slip, solid tips
- Following DIN 5254 A and DIN 5254 B, but 45° bent
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened



MM Ø 45°

General

Article No.	46 31 A12
EAN	4003773067009
Pliers	black atramentized
Head	polished
Handles	plastic coated
weight	97 g
Dimensions	130 x 86 x 11 mm

Technische Attribute

Style	3
Size of shaft	Ø 10 – 25 mm
Tips (diameter)	Ø 1.3 mm

Classification

eCl@ss 5.1.4	21040301
ETIM 5.0	EC002228
ETIM 6.0	EC002228
proficl@ss 6.0	AAC470c002
UNSPSC 13.1	27112140

technical change and errors excepted