

Product information

64 22 115 ESD

- End Cutter, mini-blade with small bevel
- High-grade special tool steel, forged, oil-hardened

Electronics End Cutting Nippers ESD

DIN ISO 9654 DIN EN 61 340-5



General

Article No.	64 22 115 ESD
EAN	4003773025061
Head	mirror polished
Handles	with multi-component grips
weight	78 g
Dimensions	115 mm
Standard	DIN ISO 9654 DIN EN 61 340-5

Technische Attribute

Cutting capacities soft wire (diameter)	Ø 0.8 mm
Head width	11 mm
	20 mm
	6 mm
	3 mm
ESD	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC002222
ETIM 6.0	EC002222
proficl@ss 6.0	AAA947c004

technical change and errors excepted