

## Product information

# 74 05 250

## High Leverage Diagonal Cutter

DIN ISO 5749

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum co-ordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



### General

|             |                            |
|-------------|----------------------------|
| Article No. | 74 05 250                  |
| EAN         | 4003773039754              |
| Pliers      | chrome plated              |
| Head        | chrome plated              |
| Handles     | with multi-component grips |
| weight      | 440 g                      |
| Dimensions  | 250 x 120 x 24 mm          |
| Standard    | DIN ISO 5749               |

### Technische Attribute

|                                                |          |
|------------------------------------------------|----------|
| Style                                          | 0        |
| Cutting capacities medium hard wire (diameter) | Ø 4.6 mm |
| Cutting capacities hard wire (diameter)        | Ø 3.5 mm |
| Cutting capacities piano wire (diameter)       | Ø 3.0 mm |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040302   |
| ETIM 5.0       | EC000165   |
| ETIM 6.0       | EC000165   |
| proficl@ss 6.0 | AAA949c004 |
| UNSPSC 13.1    | 27112114   |

technical change and errors excepted

