

Product information

78 91 125

Electronic Super Knips®

DIN ISO 9654



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Ground, very sharp cutting edges without bevel
- Precision shaped tips cut wires flush to a surface from Ø 0.2 mm.
- Shear cut with controlled micro cutting edge misalignment for the most precise cutting of even the thinnest of wires and for a long service life
- Joint with stainless steel rivet
- Extremely smooth movement for minimum operator fatigue
- With opening spring and opening limiter
- Precision-ground cutting edges with very small bevel suitable also for hard wire
- With lead catcher - no uncontrolled loss of cut wire ends
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Special tool steel, burnished

General

Article No.	78 91 125
EAN	4003773065081
Pliers	burnished
Head	burnished
Handles	with multi-component grips
weight	57 g
Dimensions	125 x 71 x 16 mm
Standard	DIN ISO 9654

Technische Attribute

Style	9
Cutting capacities medium hard wire (diameter)	Ø 1.2 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.2 – 1.6 mm
	9 mm
	7.5 mm
Head width	13.5 mm

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112149

technical change and errors excepted