

Product information

98 20 10

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdrivers for slotted screws

IEC 60900 DIN EN 60900



⚡ 1000 V ●

Allgemein

Article No.	98 20 10
EAN	4003773026396
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	184 g
Dimensions	320 x 123 x 34 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Blade length	200 mm
Length of non-insulated blade	15 mm
Handle length	120 mm
Blade width	10.0 mm
Blade thickness	1.6 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040401
ETIM 5.0	EC000158
ETIM 6.0	EC000158
proficl@ss 6.0	AAA817c008
UNSPSC 13.1	27111701

technical change and errors excepted