

## Product information

# 98 20 35 SL

## Screwdriver (Slim) for slotted screws

IEC 60900 DIN EN 60900

- Reduced blade isolation diameter for recessed spring and screw elements
- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



⚡ 1000 V 

### Allgemein

|             |                                               |
|-------------|-----------------------------------------------|
| Article No. | 98 20 35 SL                                   |
| EAN         | 4003773079712                                 |
| point       | burnished                                     |
| Handles     | insulating multi-component handle, VDE-tested |
| weight      | 42 g                                          |
| Dimensions  | 202 x 25 x 23 mm                              |
| Standard    | DIN EN 60900 IEC 60900                        |

### Technische Attribute

|                               |        |
|-------------------------------|--------|
| Blade length                  | 100 mm |
| Length of non-insulated blade | 15 mm  |
| Handle length                 | 102 mm |
| Blade width                   | 3.5 mm |
| Blade thickness               | 0.6 mm |
| VDE tested                    | yes    |

### Classification

|                |            |
|----------------|------------|
| eCl@ss 5.1.4   | 21040401   |
| ETIM 5.0       | EC000158   |
| ETIM 6.0       | EC000158   |
| proficl@ss 6.0 | AAA817c008 |
| UNSPSC 13.1    | 27111701   |

technical change and errors excepted