

Product information

98 25 01

- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel

Screwdriver for cross recessed screws

Pozidriv®

IEC 60900 DIN EN 60900



⚡ 1000V ⚡

Allgemein

Article No.	98 25 01
EAN	4003773031260
point	burnished
Handles	insulating multi-component handle, VDE-tested
weight	64 g
Dimensions	187 x 28 x 30 mm
Standard	DIN EN 60900 IEC 60900

Technische Attribute

Size	PZ1
Blade length	80 mm
Handle length	107 mm
Blade dia.	4.5 mm
Length of non-insulated blade	15 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040401
ETIM 5.0	EC000144
ETIM 6.0	EC000144
proficl@ss 6.0	AAA818c006
UNSPSC 13.1	27111701

technical change and errors excepted

Pozidriv® is a registered trademark of European Ind. Serv. Ltd.