



# 1522NW

Product no.: 1522NW

Head cutter for 1500BSF, same as 1522N, with optional safety device "wire catcher"



This is the standard head shape.



It is used for all cutting jobs in easy-to-reach areas.



The oval head provides for a high cutting capacity and is characterised by its robustness.



source images

## The Perfect Cut - Strong, sharp and precise, every time

Weller Erem pneumatic side cutters are light and precise. Thanks to a selection of different cutting heads they can operate extremely versatile. The cutters are suitable for cutting conventional components, soft metals or small plastic parts. The cutting heads can be interchanged easily.

## THE PERFECT CUT

Strong, sharp and precise - every time





### Technical Data

|                                              |                 |
|----------------------------------------------|-----------------|
| Length mm                                    | 69              |
| Length of cutting edges mm                   | 10              |
| Head width mm                                | 11              |
| Head thickness mm                            | 6               |
| Head length mm                               | 19              |
| Max. cutting capability – hard wire mm       | ---             |
| Weight in oz                                 | 1.175           |
| Length of cutting edges Inches               | 0.394           |
| Head width Inches                            | 0.433           |
| Head thickness Inches                        | 0.236           |
| Head length Inches                           | 0.748           |
| ESD-safe                                     | on              |
| Cut                                          | Flush           |
| Max. cutting capability – medium hardness mm | ---             |
| Max. cutting capability – copper wire mm     | Ø 1,6           |
| Length inches                                | 2.717           |
| Weight in g                                  | 33.3            |
| Erem applications                            | Microelectronic |