



2443P

Product no.: 2443P

Round nose pliers with very precise, smooth jaws





Pliers for miniature and standard electronics



Optimized ergonomically shaped handles for increased comfort





Non-reflecting surface, ESD-safe



source images

Built to Last - Longest lasting durability on the planet

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

Type			Type of Cut	Cutting Capacity																											
Series 2400 MagicSense				mm	0,03	0,1	0,2	0,3	0,4	0,5	0,6	0,7	0,8	0,9	1,0	1,1	1,2	1,3	1,4	1,5	1,6	1,7	1,8	1,9	2,0						
				Inch	.0001	.003	.007	.011	.015	.019	.023	.027	.031	.035	.039	.043	.047	.051	.055	.059	.062	.066	.070	.074	.078						
	2412E		Semi Flush																												
	2422E		Flush																												
	2432E		Super Full Flush																												
	2477E		Flush																												
	2403E		Flush																												
	2404E		Flush																												
	2482E		Flush																												
	2475E		Flush																												
	2470E		Flush																												
	2476TX2		Flush / Carbide																												





Technical Data

Length mm	146
Jaw length in mm	30.3
Head width mm	11
Head thickness mm	6
Width of tips in mm	0.8
Total height of both tips in mm	1.6
Length inches	5.748
Jaw length inches	1.319
Head width Inches	0.43
Head thickness Inches	0.24
Width of tips in Inches	0.031
Total height of both tips in Inches	0.063
ESD-safe	on
Erem applications	---
Material	Special tool steel
Weight in g	76
Weight in oz	2.681