

1500/...

Ściągacze dwuramienne

A
mm
S
mm

	art.	A min÷Max	L mm	L1 mm	● mm	A1 min÷Max	kg
015000301	1500/1	25÷80	100	135	17	70÷130	0,9
015000302	1500/2	25÷130	100	135	17	80÷180	1,1
015000303	1500/3	50÷160	150	210	22	105÷220	2,8
015000304	1500/4	60÷200	150	210	22	120÷270	3,1
015000305	1500/5	80÷250	205	280	27	160÷330	6,8
015000306	1500/6	80÷350	205	280	27	160÷420	8,1
015000307	1500/7	110÷520	205	280	27	195÷600	12,5
015000308	1500/8	170÷640	230	310	36	260÷715	23,3

