







Notes:

1.Material:PA6 UL94 V2

2.Color:Black;

3.RoHS Compliant;

Part No.	Part Name	Hole	Panel Thickness	A	B	C	D
20667	8G418V20667	3.6-3.7	2.0-3.5	6.4	1.6	9.5	7.1
20734	8G418V20734		3.5-5.0			11.5	9.0
20735	8G418V20735		5.0-6.5			13.5	11.0
20666	8G418V20666	4.1-4.2	2.0-3.5	8.0	1.8	10.0	7.1
20736	8G418V20736		3.5-5.5			12.0	9.0
20737	8G418V20737		5.5-7.5			14.0	9.0
20665	8G418V20665	4.9-5.0	2.0-4.0	9.0	2.2	11.0	8.5
20738	8G418V20738		4.0-6.0			13.0	10.5
20739	8G418V20739		6.0-8.0			14.5	12.0

DREMEC Befestigungselemente GmbH						DATE	2021.03.31	DIMENSION	TOLERANCE
TITLE	PUSH RIVET					SCALE	FIT	$L \leq 4$	± 0.10
PART NAME	D8G418V20667	MOLD NO.	/	DRAW	JF	UNIT	MM	$4 < L \leq 15$	± 0.20
PART NO.	SEE STABLE	MATERIAL	SEE NOTES	DESIGN	JF	VERSION	A0	$15 < L \leq 50$	± 0.30
DWG NO.	E2181	COLOR	SEE NOTES	APPROVAL	FDL	VIEW		$50 < L \leq 100$	± 0.40