

VK001011
CONNECTION TECHNOLOGY • DISTRIBUTION TERMINALS

distributor, 2x M12 3pin, M12 4pin, TPU


MECHANICAL FEATURES

Angle of the slots	90 °
Housing material	TPU

ELECTRICAL FEATURES

Number of pins	4
Number of pins of sensor/actuator slots	3
Number of sensor/actuator slots	2
Rated switching current	4000 mA
Type of branches for sensor/actuator cables	M12
Type of plug connector for trunk line	M12
Voltage type	AC/DC
With LED display	-


Other

Packaging dimensions	100mm x 0.0mm x 120mm
Shipping weight	
Tariff code	85366990

Classification

ipf product group	855
eClass 8.0	27279219
eClass 9.0	27440108
eClass 9.1	27440108
ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585

Connection



Dimensional drawing

Installation



Mounting / installation may only be carried out by a qualified electrician!

Disposal



Safety warnings

Before initial operation, please make sure to follow all safety instructions that may be provided in the product information. Never use these devices in applications where the safety of a person depends on their functionality. LED lighting systems can generate intensive UV radiation, which can damage your eyes in case of improper use. The manufacturer cannot be held responsible for damages that result from improper use or connection.