

# Hex Key & Set

KT No. & D1

- Material - SNCM - V alloy steel
- Finishing - chrome plated

## 1145MR

- Standard arm type
- Allen head
- DIN ISO 2936



| KT NO.   | mm   | mm | mm  | g   | kg       |
|----------|------|----|-----|-----|----------|
| 114515MR | H1.5 | 16 | 47  | 1   | 20 / 400 |
| 114502MR | H2   | 18 | 52  | 1   | 20 / 400 |
| 114525MR | H2.5 | 21 | 59  | 3   | 20 / 400 |
| 114503MR | H3   | 24 | 66  | 5   | 20 / 400 |
| 114504MR | H4   | 30 | 74  | 10  | 20 / 400 |
| 114505MR | H5   | 33 | 85  | 18  | 20 / 400 |
| 114555MR | H5.5 | 36 | 91  | 23  | 10 / 200 |
| 114506MR | H6   | 38 | 97  | 29  | 10 / 200 |
| 114507MR | H7   | 41 | 102 | 43  | 10 / 200 |
| 114508MR | H8   | 44 | 108 | 58  | 10 / 200 |
| 114510MR | H10  | 50 | 122 | 101 | 10 / 200 |

## 1125MR

- Extra long arm type
- Allen head
- DIN ISO 2936

| KT NO.   | mm   | mm  | mm  | g    | kg       |
|----------|------|-----|-----|------|----------|
| 112515MR | H1.5 | 16  | 92  | 1    | 20 / 400 |
| 112502MR | H2   | 18  | 102 | 3    | 20 / 400 |
| 112525MR | H2.5 | 21  | 115 | 5    | 20 / 400 |
| 112503MR | H3   | 23  | 129 | 9    | 20 / 480 |
| 112504MR | H4   | 29  | 144 | 17   | 20 / 300 |
| 112505MR | H5   | 33  | 165 | 31   | 20 / 300 |
| 112506MR | H6   | 38  | 186 | 51   | 20 / 400 |
| 112507MR | H7   | 41  | 197 | 74   | 20 / 240 |
| 112508MR | H8   | 44  | 208 | 100  | 10 / 100 |
| 112510MR | H10  | 50  | 234 | 176  | 10 / 100 |
| 112512MR | H12  | 57  | 262 | 286  | 8 / 48   |
| 112514MR | H14  | 70  | 294 | 445  | 8 / 48   |
| 112517MR | H17  | 80  | 337 | 770  | 4 / 32   |
| 112519MR | H19  | 89  | 380 | 863  | 4 / 16   |
| 112522MR | H22  | 102 | 422 | 1590 | 4 / 16   |

## 1145SR

| KT NO.   | inch | mm | mm  | g   | kg       |
|----------|------|----|-----|-----|----------|
| 114502SR | 1/16 | 18 | 49  | 1   | 20 / 400 |
| 114525SR | 5/64 | 20 | 52  | 1.5 | 20 / 400 |
| 114503SR | 3/32 | 21 | 56  | 3   | 20 / 400 |
| 114504SR | 1/8  | 25 | 63  | 5   | 20 / 400 |
| 114505SR | 5/32 | 28 | 70  | 9   | 20 / 400 |
| 114506SR | 3/16 | 31 | 77  | 15  | 20 / 400 |
| 114508SR | 1/4  | 37 | 91  | 31  | 10 / 200 |
| 114510SR | 5/16 | 42 | 106 | 55  | 10 / 200 |
| 114512SR | 3/8  | 47 | 120 | 93  | 10 / 120 |
| 114516SR | 1/2  | 54 | 146 | 195 | 10 / 120 |
| 114518SR | 9/16 | 59 | 160 | 267 | 6 / 72   |
| 114520SR | 5/8  | 64 | 175 | 362 | 6 / 72   |
| 114524SR | 3/4  | 73 | 203 | 599 | 6 / 24   |

## 1125SR

| KT NO.   | inch | mm | mm  | g   | kg       |
|----------|------|----|-----|-----|----------|
| 112502SR | 1/16 | 16 | 92  | 2   | 20 / 400 |
| 112525SR | 5/64 | 18 | 102 | 3   | 20 / 400 |
| 112503SR | 3/32 | 21 | 115 | 5   | 20 / 400 |
| 112504SR | 1/8  | 23 | 129 | 9   | 20 / 400 |
| 112505SR | 5/32 | 29 | 144 | 17  | 20 / 300 |
| 112506SR | 3/16 | 33 | 165 | 28  | 20 / 300 |
| 112508SR | 1/4  | 38 | 186 | 57  | 10 / 100 |
| 112510SR | 5/16 | 44 | 208 | 100 | 10 / 100 |
| 112512SR | 3/8  | 50 | 234 | 160 | 10 / 100 |
| 112516SR | 1/2  | 57 | 262 | 319 | 8 / 48   |
| 112518SR | 9/16 | 70 | 294 | 459 | 8 / 48   |



| KT NO.    | PC. | Spec.          | Contents                                          | kg   | kg      |
|-----------|-----|----------------|---------------------------------------------------|------|---------|
| 20218MR   | 8   | knife type     | H2, H2.5, H3, H4, H5, H6, H8, H10                 | 0.29 | 12 / 72 |
| 20219MR   | 9   | Standard arm   | H1.5, H2, H2.5, H3, H4, H5, H6, H8, H10           | 0.33 | 6 / 48  |
| 20219SR   | 9   |                | 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, 5/16, 3/8 | 0.33 | 6 / 48  |
| 20208MR   | 8   | Extra long arm | H2, H2.5, H3, H4, H5, H6, H8, H10                 | 0.43 | 8 / 48  |
| 20209MR   | 9   |                | H1.5, H2, H2.5, H3, H4, H5, H6, H8, H10           | 0.49 | 8 / 48  |
| 20209SR02 | 9   |                | 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, 5/16, 3/8 | 0.47 | 8 / 48  |