

SILVYN® K-EM

SILVYN® K-EM - end cap for parallel corrugated conduits



Reliability

Benefits

- Easy to assemble
- High temperature resistance
- Cable damage can be prevented
- Additional sealing

Application range

In combination with protective conduit:
SILVYN® RILL PA 6
SILVYN® RILL PA 12
Intersection or end sleeve

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000519

ETIM 5.0 Class-Description: Terminal sleeve for protective hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000519

ETIM 6.0 Class-Description: Terminal sleeve for protective hose

Colour delivered:

Grey (RAL 7031)

Black (RAL 9011), UV-resistant

Material:

TPE-V

Temperature range:

-40°C to +120°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® K-EM

Article number	Nominal size	Overall length mm	For conduit with outer Ø (mm)	Pieces / PU
SILVYN® K-EM grey				
65500200	10	29	10	50
65500210	13	32.5	13	50
65500220	16	36.5	15.8	50
65500230	21	37.5	21.2	50
65500240	28	40.2	28.5	25
65500250	34	44.2	34.5	25
65500260	42	46	42.5	25
65500270	54	52	54.5	10
SILVYN® K-EM black				
65500205	10	29	10	50
65500215	13	32.5	13	50
65500225	16	36.5	15.8	50
65500235	21	37.5	21.2	50
65500245	28	40.2	28.5	25
65500255	34	44.2	34.5	25
65500265	42	46	42.5	25
65500275	54	52	54.5	10