


| SYM | DESCRIPTION | APPROVED | DATE |
|-----|-------------|----------|------|
| 1   |             |          |      |
| 2   |             |          |      |
| 3   |             |          |      |
| 4   |             |          |      |



|     |      |             |         |                                                                                                 |             |                    |                      |          |              |                                                                                                                                               |  |  |
|-----|------|-------------|---------|-------------------------------------------------------------------------------------------------|-------------|--------------------|----------------------|----------|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| 13  |      |             |         | Tolerance (mm)                                                                                  |             |                    |                      |          |              |                                                                                                                                               |  |  |
| 12  |      |             |         | Wire harness size<br>L(mm)                                                                      | Trunk       | Protection<br>tube | Positioning<br>space | APPROVED | Shen Juan    | <div></div> <div>Jiaxing Lau Electronics Co., Ltd.</div> |  |  |
| 11  |      |             |         | L≤200                                                                                           | +20<br>-10  |                    | ±5                   |          |              |                                                                                                                                               |  |  |
| 10  |      |             |         | 200<L≤500                                                                                       | +25<br>-10  |                    | ±5                   |          |              |                                                                                                                                               |  |  |
| 9   |      |             |         | 500<L≤1000                                                                                      | +40<br>-20  |                    | ±10                  |          |              |                                                                                                                                               |  |  |
| 8   |      |             |         | 1000<L≤2000                                                                                     | +60<br>-20  |                    | ±20                  | CHECKED  | Li Jie       | Customer :<br><br>Date :<br>2021-4-8                                                                                                          |  |  |
| 7   |      |             |         | 2000<L≤3000                                                                                     | +60<br>-30  |                    | ±30                  |          |              |                                                                                                                                               |  |  |
| 6   |      |             |         | 3000<L≤5000                                                                                     | +60<br>-30  |                    | ±30                  | DRAWN    | Zhang Yining | DRAWING NO.<br>DC2200. 0150E<br><br>SIZE:<br>A4                                                                                               |  |  |
| 5   |      |             |         | L> 5000                                                                                         | +100<br>-50 |                    | ±40                  |          |              |                                                                                                                                               |  |  |
| 4   |      |             |         | <div></div> |             |                    |                      | UNIT     | mm           | CUSTOMER NO.<br><br>PAGE:<br>1/1                                                                                                              |  |  |
| 3   |      |             |         |                                                                                                 |             |                    |                      | REV      | B            |                                                                                                                                               |  |  |
| 2   |      |             |         |                                                                                                 |             |                    |                      |          |              |                                                                                                                                               |  |  |
| 1   |      |             |         |                                                                                                 |             |                    |                      |          |              |                                                                                                                                               |  |  |
| SYM | Name | Description | Remarks |                                                                                                 |             |                    |                      |          |              |                                                                                                                                               |  |  |