


| SYM | DESCRIPTION | APPROVED | DATE |
|-----|-------------|----------|------|
| 1   |             |          |      |
| 2   |             |          |      |
| 3   |             |          |      |
| 4   |             |          |      |



|     |      |             |         |                                                                                      |             |                    |                      |          |              |                                                                                                                                               |               |              |
|-----|------|-------------|---------|--------------------------------------------------------------------------------------|-------------|--------------------|----------------------|----------|--------------|-----------------------------------------------------------------------------------------------------------------------------------------------|---------------|--------------|
| 13  |      |             |         | Tolerance (mm)                                                                       |             |                    |                      | APPROVED | Shen Juan    | <div></div> <div>Jiaxing Lau Electronics Co., Ltd.</div> |               |              |
| 12  |      |             |         | Wire harness size<br>L(mm)                                                           | Trunk       | Protection<br>tube | Positioning<br>space |          |              |                                                                                                                                               |               |              |
| 11  |      |             |         | L≤200                                                                                | +20<br>-10  |                    | ±5                   | CHECKED  | Li Jie       |                                                                                                                                               |               |              |
| 10  |      |             |         | 200<L≤500                                                                            | +25<br>-10  |                    | ±5                   |          |              |                                                                                                                                               |               |              |
| 9   |      |             |         | 500<L≤1000                                                                           | +40<br>-20  |                    | ±10                  | DRAWN    | Zhang Yining | Customer :                                                                                                                                    | Date :        | 2021-4-8     |
| 8   |      |             |         | 1000<L≤2000                                                                          | +60<br>-20  |                    | ±20                  |          |              |                                                                                                                                               |               |              |
| 7   |      |             |         | 2000<L≤3000                                                                          | +60<br>-30  |                    | ±30                  |          |              |                                                                                                                                               |               |              |
| 6   |      |             |         | 3000<L≤5000                                                                          | +60<br>-30  |                    | ±30                  | UNIT     | mm           | DRAWING NO.                                                                                                                                   | DC2601. 0025E | SIZE:<br>A4  |
| 4   |      |             |         | L> 5000                                                                              | +100<br>-50 |                    | ±40                  |          |              | CUSTOMER NO.                                                                                                                                  |               | PAGE:<br>1/1 |
| 3   |      |             |         |  |             |                    |                      | REV      | B            |                                                                                                                                               |               |              |
| 2   |      |             |         |                                                                                      |             |                    |                      |          |              |                                                                                                                                               |               |              |
| 1   |      |             |         |                                                                                      |             |                    |                      |          |              |                                                                                                                                               |               |              |
| SYM | Name | Description | Remarks |                                                                                      |             |                    |                      |          |              |                                                                                                                                               |               |              |