

Tap & Die Set

12916MQ1

- Material : SK5 alloy steel
- 1 PC. Tap wrench(M3-M12, 1/8"~1/2")
- 1 PC. Die stock 25mm(1")
- Tap : M3~M12
- Die : M3~M12

Contents		Kg 0.78	1 / 20
12939MQ-A	M3x0.5, M4x0.7, M5x0.8, M6x1.0, M8x1.25, M10x1.5, M12x1.75	12939MQ-A01	25mm (1")
12939MQ-A		12939MQ-A02	M3~M12 (1/8"~1/2")



16 PC.

12939MQ1

- Material : SK5 alloy steel
- 1 PC. Tap wrench(M3-M12, 1/8"~1/2")
- 1 PC. "T" Type tap wrench(M3-M6, 1/8"~1/4")
- 1 PC. Die stock 25mm(1")
- 1 PC. Screw driver
- 12939MQ1-
1 PC. Screw pitch gauge (0.5-28)
Tap : M3~M12 / Die: M3~M12
- 12939SQ1-
1 PC. Screw pitch gauge(12-40)
Tap : 1/8"~1/2" / Die : 1/8"~1/2"



12939SQ1



39 PC.

KT NO.	Contents		Kg 1.4	1 / 10
12939MQ1	12939MQ-A	12939MQ-A06 / M3x0.5, 12939MQ-A07 / M3x0.6, 12939MQ-A08 / M4x0.7, 12939MQ-A09 / M4x0.75, 12939MQ-A10 / M5x0.8, 12939MQ-A11 / M5x0.9, 12939MQ-A12 / M6x0.75, 12939MQ-A13 / M6x1.0, 12939MQ-A14 / M7x0.75, 12939MQ-A15 / M7x1.0, 12939MQ-A16 / M8x1.0, 12939MQ-A17 / M8x1.25, 12939MQ-A18 / M10x1.25, 12939MQ-A19 / M10x1.5, 12939MQ-A20 / M12x1.5, 12939MQ-A21 / M12x1.75, 12939MQ-A22 / 1/8NPT27	12939MQ-A01	25mm (1")
	12939MQ-A	12939MQ-A23 / M3x0.5, 12939MQ-A24 / M3x0.6, 12939MQ-A25 / M4x0.7, 12939MQ-A26 / M4x0.75, 12939MQ-A27 / M5x0.8, 12939MQ-A28 / M5x0.9, 12939MQ-A29 / M6x0.75, 12939MQ-A30 / M6x1.0, 12939MQ-A31 / M7x0.75, 12939MQ-A32 / M7x1.0, 12939MQ-A33 / M8x1.0, 12939MQ-A34 / M8x1.25, 12939MQ-A35 / M10x1.25, 12939MQ-A36 / M10x1.5, 12939MQ-A37 / M12x1.5, 12939MQ-A38 / M12x1.75, 12939MQ-A39 / 1/8NPT27	12939MQ-A02	M3~M12 (1/8"~1/2")
	12939MQ-A03	0.5, 0.6, 0.7, 0.75, 0.8, 0.9, 1.0, 1.25, 1.5, 1.75, 27, 28	12939MQ-A04	M3~M6 (1/8"~1/4")
12939SQ1	12939SQ-A	4NS36, 6NC32, 8NC32, 10NC24, 10NF32, 12NC24, 1/4NC20, 1/4NF28, 5/16NC18, 5/16NF24, 3/8NC16, 3/8NF24, 7/16NC14, 7/16NF20, 1/2NC13, 1/2NF20, 1/8NPT27	12939MQ-A05	
	12939SQ-A	12, 13, 14, 16, 18, 20, 24, 27, 28, 32, 36, 40		

