


Metal fitting

Item number 1570326050



Technical data

Material	Nickel-plated brass
Protection class	IP 54
Temperature range	-20°C to +80°C
Variant	Metric
External thread (AG)	M32
d	23 mm
Thread length (GL)	12 mm
Height (H)	31 mm
Wrench size (SW)	35 mm
Suitable for metal hose DN	26

Metal fitting

Item number 1570326050

Commercial data

Packaging Unit	15
EAN code	4033878426173
Weight	0.072 kg
ETIM 7	EC001180
ETIM 8	EC001180
eCl@ss 10.1	27-43-03-10
Customs tariff number	74122000

Note:

