





Notes:
1.RoHS Compliant;
2.Hole: Ø2.54±0.05mm;
Panel Thickness: 1.63mm.

Part No.	Part Name	Part No.	Part Name	Part No.	Part Name	A
40194	D8G821V40194	40195	D8G821V40195	40196	D8G821V40196	1.6
40197	D8G821V40197	40198	D8G821V40198	43192	D8G821V43192	3.2
40200	D8G821V40200	40201	D8G821V40201	43193	D8G821V43193	4.8
40202	D8G821V40202	40203	D8G821V40203	43194	D8G821V43194	6.4
40204	D8G821V40204	40205	D8G821V40205	40206	D8G821V40206	7.9
40207	D8G821V40207	40208	D8G821V40208	43195	D8G821V43195	9.5
40209	D8G821V40209	40210	D8G821V40210	43196	D8G821V43196	11.1
40211	D8G821V40211	40212	D8G821V40212	43197	D8G821V43197	12.7
40213	D8G821V40213	40214	D8G821V40214	40215	D8G821V40215	14.3
40216	D8G821V40216	40217	D8G821V40217	40218	D8G821V40218	15.9
42448	D8G821V42448	42449	D8G821V42449	43198	D8G821V43198	22.2
Material: PA66 UL94 V2 Color: Natural		Material: PA66 UL94 V0 Color: Natural		Material: PA66 UL94 V2 Color: Yellow		

Part No.	Part Name	Part No.	Part Name	A
43173	D8G821V43173	43174	D8G821V43174	1.6
40199	D8G821V40199	43175	D8G821V43175	3.2
43176	D8G821V43176	43177	D8G821V43177	4.8
43178	D8G821V43178	43179	D8G821V43179	6.4
43171	D8G821V43171	43180	D8G821V43180	7.9
43181	D8G821V43181	43182	D8G821V43182	9.5
43183	D8G821V43183	43184	D8G821V43184	11.1
43172	D8G821V43172	43185	D8G821V43185	12.7
43186	D8G821V43186	43187	D8G821V43187	14.3
43188	D8G821V43188	43189	D8G821V43189	15.9
43190	D8G821V43190	43191	D8G821V43191	22.2
Material: PA66 UL94 V2 Color: Black		Material: PA66 UL94 V0 Color: Black		

DREMEC Befestigungselemente GmbH						DATE	2021.03.10	DIMENSION	TOLERANCE
TITLE	PUSH SPACER					SCALE	FIT	L ≤ 4	±0.10
PART NAME	D8G821V40194	MOLD NO.	S0301/2	DRAW	PLK	UNIT	MM	4 < L ≤ 15	±0.20
PART NO.	SEE TABLE	MATERIAL	SEE TABLE	DESIGN	PLK	VERSION	A0	15 < L ≤ 50	±0.30
DWG NO.	E4014	COLOR	SEE TABLE	APPROVAL	FDL	VIEW		50 < L ≤ 100	±0.40