

Flexiamant 230x3.0x22.23 steel, TF 41 (616127000)

Order no. 616127000

EAN 4007430400246



Product may differ from Image

- Universal disc for complete metal processing
- Hardness: medium
- High cutting output with long tool life
- Uniform in cutting output and tool life
- Maximum working speed 80 m/s

Technical data

Characteristics

Quality class	A 30-R
Diameter x thickness x bore	230 x 3 x 22.23 mm
Version	straight
Maximum speed	6600 rpm
Sales unit / packaging unit	1 / 25