

Flexiarapid 115x1.0x22.23 Inox, TF 41 (616186000)

Order no. 616186000

EAN 4007430445421



Product may differ from Image

- Thin high-output cutting disc especially for stainless, thin-walled materials such as pipes, metal sheets, profiles, wires
- Hardness: hard
- Very high cutting output with good tool life by using special corundums
- Low material consumption, power-saving, low machine load.
- Low in iron, sulphur and chlorine ($\text{Fe} + \text{S} + \text{Cl} \leq 0.1\%$)
- Maximum working speed 80 m/s
- A 60-R with 1 mm thickness; A 46-R with 1.6 mm thickness; A 30-R with 1.9 mm thickness

Technical data

Characteristics

Quality class	A 60-R
Diameter x thickness x bore	115 x 1 x 22.23 mm
Version	straight
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25