

Flexiamant super 125x6.0x22.23 steel, SF 27 (616486000)

Order no. 616486000

EAN 4007430435880



Product may differ from Image

- Universal disc for all metal processing requirements
- Especially suitable for deburring and grinding edges, also for cast processing
- Hardness: hard
- Good cutting output with extremely good tool life
- Maximum working speed 80 m/s

Technical data

Characteristics

Quality class	A 24-T
Diameter x thickness x bore	125 x 6 x 22.23 mm
Version	offset
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25