

**Novoflex 125x2.5x22.23 steel, TF 41 (616444000)**

Order no. 616444000

EAN 4007430433909



Product may differ from Image

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting performance with good tool life.
- Maximum working speed 80 m/s
- Arbeitshöchstgeschwindigkeit 80 m/s

## Technical data

### Characteristics

|                             |                      |
|-----------------------------|----------------------|
| Quality class               | A 30                 |
| Diameter x thickness x bore | 125 x 2.5 x 22.23 mm |
| Version                     | straight             |
| Maximum speed               | 12200 rpm            |
| Sales unit / packaging unit | 1 / 25               |