

Novoflex 150x6.0x22.23 steel, SF 27 (616464000)

Order no. 616464000

EAN 4007430434043



Product may differ from Image

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting output with good tool life
- Maximum working speed 80 m/s

Technical data

Characteristics

Quality class	A 24
Diameter x thickness x bore	150 x 6 x 22.23 mm
Version	offset
Maximum speed	10200 rpm
Sales unit / packaging unit	1 / 25