

Diamond drill bits for tiles "Dry", 60 mm, M14 (628313000)

Order no. 628313000

EAN 4007430230669



Product may differ from Image

- M14 Thread for use on angle grinders
- Long service life and fast drilling progress thanks to vacuum hard soldered diamonds
- Easy removal of the drill core thanks to lateral recesses
- No extra cooling required. For Ø 6-14 mm an additional paraffin emulsion is integrated for improved cooling. We recommend to briefly cool the tip with water in case of drilling in quick succession!
- We recommend using the thickness of the tile / fine earthenware / granite board as useful length. As a rule, max. 2 cm granite boards / work boards up to 5 cm can be drilled. Retract the drill bit often from the drilled hole so that it can cool down!
- Important: Do not drill into the subsurface in case of laid material!
- Maximum working speed: 80 m/s

Technical data

Characteristics

Diameter	60 mm
Overall length	91 mm
Sales unit	1