

Saw blade "multi cut - professional", 216x30, Z60 FZ/TZ, 5°neg. (628083000)

Order no. 628083000

EAN 4007430176509



Product may differ from Image

- Universal use for demanding materials
- For the highest standards in cutting quality, e.g. for laminate, thin-walled plastic, aluminium, copper and bronze materials
- Ideally suited for many interior work applications
- Perfect cutting results, also for cross-cuts in solid wood, coarse, coated or veneered chipboards, MDF
- The circular saw must have a very high performance power
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Technical data**Characteristics**

Diameter x cutting width x bore	216 x 2.4 x 30 mm
Material	HW/CT
Number of teeth	60
Tooth shape	FZ/ TZ
Steel blade thickness	1.8 mm
Rake angle	5° neg.
Suitable for	KS 216 M Lasercut / KGS 216 M / KGS 216 Plus / KGSV 216 M / KGSV 72 Xact / KGSV 72 Xact SYM
Packaging	Cardboard box