

Protection window PW 343009T



Order symbol: PW 343009 T
Product nbr: 4901824
Description: Protection Window
Remarks:

EAN: 6418074309747
El. number:
Finland:
Denmark:
Electric No.
Sweden:

Including: Cover transparent, frame grey, installation material and drilling template.

Dimension	Length	Width	Height	Rating:
mm:	340	300	90	Ingress Protection (EN 60529): IP66
inch:	13.5	11.6	3.5	Impact Resistance (EN 62262): IK09

NEMA Class: NEMA 1, 4, 4X, 12, 13

Materials:

Material: Polycarbonate
Frame colour: Grey
Cover colour: Transparent
Gasket material: Polyurethane

Certificates:

SGS Fimko

Temperatures:

Temperature °C (short term): -40 ... 120 °C
Temperature °C (continuous): -40 ... 80 °C
Temperature °F (short term): -60 ... 248 °F
Temperature °F (continuous): -60 ... 176 °F

