

Bit Set

- Silicon chrome vanadium alloy steel (S2)
- Anti-rust oiled, sand-blasted

1011MQ

Metal case size (mm) : 198 x 105 x 37 (0.027 cuft)



11
PC.

Contents

0.82 1 / 20

1636M	M5, M6, M8, M10, M12
1680M	M5, M6, M8, M10, M12
414810M	

1015MQ

Metal case size (mm) : 198 x 105 x 37 (0.027 cuft)



15
PC.

Contents

0.96 1 / 20

1636H	H4, H5, H6, H7, H8, H10, H12
1680H	H4, H5, H6, H7, H8, H10, H12
414810M	

1015PQ

Metal case size (mm) : 198 x 105 x 37 (0.027 cuft)



15
PC.

Contents

0.90 1 / 20

1636T	T20, T25, T30, T40, T45, T50, T55
1680T	T20, T25, T30, T40, T45, T50, T55
414810M	

1023EQ

Metal case size (mm) : 244 x 118 x 37 (0.038 cuft)



23
PC.

Contents

1.60 1 / 18

1636E	10IP, 15IP, 20IP, 25IP, 27IP, 30IP, 40IP, 45IP, 50IP, 55IP, 60IP
1680E	10IP, 15IP, 20IP, 25IP, 27IP, 30IP, 40IP, 45IP, 50IP, 55IP, 60IP
414810M	

1040CQ

new

Metal case size (mm) : 320 x 153 x 31 (0.054 cuft)



40
PC.

Contents

2.0 1 / 10

1630M	M5, M6, M8, M10, M12
1630H	H4, H5, H6, H7, H8, H10, H12
1630T	T20, T25, T30, T40, T45, T50, T55
1675M	M5, M6, M8, M10, M12
1675H	H4, H5, H6, H7, H8, H10, H12
1675T	T20, T25, T30, T40, T45, T50, T55
314810M, 414810M	

1042CQ

Metal case size (mm) : 205 x 80 x 42 (0.024 cuft)



42
PC.

Contents

0.52 1 / 20

1025H	H1.5, H2, H2.5, H3, H4, H5, H6, H7, H8, H10
1025T	T6
1025U	T7H, T8H, T9H, T10H, T15H, T20H, T25H, T27H, T30H, T40H
1025S	3 x 0.5, 3.5 x 0.6, 4 x 0.5, 4.5 x 0.6, 5 x 0.8, 5.5 x 0.8, 6 x 1.0, 6.5 x 1.2, 7 x 1.2, 8 x 1.2
1025P	PH0, PH1, PH2, PH3
1025Z	PZ1, PZ2, PZ3
1025R	RB0, RB1, RB2, RB3

1043CQ

Metal case size (mm) : 290 x 130 x 41 (0.056 cuft)



43
PC.

Contents

2.50 1 / 10

1636H	H4, H5, H6, H7, H8, H10, H12
1636M	M5, M6, M8, M10, M12
1636T	T20, T25, T27, T30, T40, T45, T50, T55, T60
1680H	H4, H5, H6, H7, H8, H10, H12
1680M	M5, M6, M8, M10, M12
1680T	T20, T25, T27, T30, T40, T45, T50, T55, T60
414710M	

