



NOTE :-

- 1) ALL SHARP EDGES ARE BURR FREE.
- 2) NON DIMENSIONAL RADIUS - 2.0mm
- 3) ALL CORNERS ARE FILLET WELDED AND GRINDED.
- 4) IP RATING - IP 65
- 5) TOLERANCE AS PER DIN ISO 2768-mK

ALL RIGHTS RESERVED AND/OR PHOTOCOPYING THIS DOCUMENT TO A PERSON WITHOUT RaychemPG (P)LTD WRITTEN AUTHORIZATION IS PROHIBITED

Item No.	Description	Material	Drawing No.	Rev. No.	Qty	PON
1	20X105X100 Base	GI	FR-03-L	0	1	
2	20X105X100 Ld	GI	FR-03-L	0	1	DAB4101010
3	MS Self Lunge Flanged Stamped Nut&st	SS 304	RPPL STD	0	4	
4	Oxal Head Screw DN 966-455-33	SS 304	RPPL STD	0	4	DAB4100613
5	Special Insert for MS to screw	PA	RPPL STD	0	4	DAB4700021
6	SILICONE W/O SPONGE PFOHFE 1.3 X 7 MM with one side SELF-ADHESIVE TAPE AS PER DRAWING 1010-S1-GSK	Silicone	2015-S1-GSK	0	0.65m	DA-P07/00003
7	Mounting Plate	MS ZN, PL	FR-03-WP	0	1	
8	M6x12 Earth Stud	SS 304	STD	0	1	DAB4101210
9	M8x6 EARTHING SCREW - COPPER PLATED	MS Cu, PL	STD	0	4	MAAA0030109
10	CB16-3H + CONNECTING 10 mm ² 3 TERMINAL BLOCK	Ceramic		0	3	DAB4100780
11	FLAT SLOTTED HEAD M3X20 MS SCREW FOR CB16-3H 3 TERMINAL BLOCK	MS ZN, PL	STD	0	6	DAB4100181
12	FR SIZE LABEL	Polyester	FR-03-LB	0	1	MAAA007073
13	FR LABEL BS93957	Polyester	FR-03-LB-00	0	1	MAAA007074

REV. NO.	-	-	-	-	-	-	-	-	-
DESCRIPTIONS									
Ref: RPPL	TITLE: .FR JUNCTION BOX			200X150X100 ASSY					
Tolerances DIN ISO 2768mK		MATERIAL: Gl 1.5mm		FINISH: POWDER COATED RAL2005 ORANGE (100% Editions)		PART NO.: DAA6400032		DRG. NO. FRJ03-A	
 FIRST ANGLE PROJECTION  THIRD ANGLE PROJECTION		Raychem RPPL (P) Limited 02, Annle Desam Road, Chennai - 600 008 Web : www.raychem.com							
DO NOT SCALE									CHECKED 