




- NOTE :-**
- 1) ALL SHARP EDGES ARE BURR FREE.
 - 2) NON DIMENSIONAL RADIUS - 2.0mm
 - 3) ALL CORNERS ARE FILLET WELDED AND GRIINDED
 - 4) IP RATING - IP 65
 - 5) TOLERANCE AS PER DIN ISO 2768-mK
- FUNCTIONAL DIMENSIONS**

Item No.	Description	Material	Drawing No.	Rev. No.	Qty	PON
1	350Z/250X105 Base	GI	FRJ06-L	0	1	DAB101213
2	350Z/250X105 Lid	GI	FRJ06-L	0	1	DAB101213
3	MS Blind Lead Flanged Sterilized Nut/Sert	SS 304	FRJEL STD	0	4	DAB100613
4	Oval Head Screw D16 95X6X33	SS 304	FRJEL STD	0	4	DAB100613
5	Stainless Insert for D16 size screw	PA	FRJEL STD	0	4	DAB4700621
6	7.6mm with ONE SIDE SELF ADHESIVE TAPE AS PER DRAWING 10105/SI/SGSK	Silicone	352S-SI/SGSK	0	1.2m	JAP0100003
7	Mounting Plate	MS 24 PL	FRJ06-MP	0	1	DAB101213
8	MS X 12 Earth Stud	MS 24 PL	STD	0	1	MAA0030109
9	M8X8 EARTHING SCREW - COPPER PLATED	MS CO. PL	STD	0	6	MAA0030109
10	CB16/3H - CONNECTIV 10 mmφ 3 POL. WITH MOUNT HOLE CERAMIC	Ceramic	STD	0	4	DAB100781
11	FLAT SLOTTED HEAD M3X20 MS SCREW FOR CB16/3H TERMINAL BLOCK	MS 24 PL	STD	0	8	DAB100781
12	SIZ. LABEL B56X97	Polyester	FRJ06-LB	0	1	MAA007076
13	FRJ06-LB	Polyester	FRJ06-LB	0	1	MAA007076

REV. NO.	DESCRIPTIONS		DATE	DRAWN	CHECKED
Ref: RPPL	TITLE: - FR JUNCTION BOX 350x250x105 ASSY	MATERIAL:- GI 1.5mm	27/11/18	PRAN	DHAN
		FINISH:- POWDER COATED RAL2003 ORANGE (100% Solubles)	P.W./	CHECKED	
 FPEI INDIA PRODUCTION ALL INFORMATION ARE IN MM		PART NO.: DAA6d00035			
Raychem RPE (P) Limited Cstt Mahal Avenue, Dt. Anaple Baramal Road, Wd. www.raychem.com		DRG. NO. FRJ06-A			
DO NOT SCALE					