


Measuring leads

BNC AL 0,64



Product	BNC AL 0,64
description	BNC - adapter lead with insulated socket for 0.64 mm round pillar and 0.64 mm rectangular pillar. Red inner lead, black shielding, for use with oscilloscopes, PC-card, ... cable typ: RG 58 A/U, 50 Ohm
operating instruction	BA001
Articlenummer	933844001
drawing	
	
technical data	
rated voltage ⁽¹⁾	30 VAC / 60 VDC
temperature range acc. To IEC61010 ⁽²⁾	-15 °C to +70 °C
cable length	120 cm

⁽¹⁾ for normal environmental conditions -5°C to +40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

stand: 20.07.2018