

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300580059

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

RJ-Lnxx RJ45 Female to RJ45 Female Adaptor, Panel Mount Pass Thru



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Field Attachable / Accessories
Series	130058
IP Rating	IP67
Material - Contact	N/A
Overview	Brad Industrial Ethernet Solutions
Product Name	RJ-Lnxx
Taxonomy	Circular Industrial Connectors
Type	Threaded Interconnect
UPC	78678856747
Physical	
Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	N/A
Material - Connector Body	Delrin
Material - Coupling Nut	Nylon
Material - Plating Mating	n/a
Net Weight	68.038/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V DC
Material Info	
Engineering Number	RJBG17946
Reference - Drawing Numbers	
Sales Drawing	SD-130058-007-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/30/2017 (7 July 2017)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of	CER_4000409978_00_000.pdf
Conformity	
ZZCERT_UKCA - Declaration of	CER_4000410292_00_000.pdf
Conformity	

Search Parts in this Series

130058 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION