

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1727040032

Status:


Active

Overview:

FCT D-Sub Connectors

Description:

FCT Mixed Layout D-Sub Housing, Female, Tin-plated Shell without Dimples, 3 Circuits



Documents:	
Drawing (PDF)	Brochure (PDF)
Datasheet (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	D-Sub Products
Series	172704
IP Rating	IP20
Overview	FCT D-Sub Connectors
Product Category	D-Sub Connector
Product Name	FCT Products
Taxonomy	D-Sub Connectors
Type	Mixed Layout
UPC	889056019439
Physical	
Circuits (Loaded)	0
Circuits (maximum)	3
Color - Resin	Green
Gender	Female
Material - Resin	PBT
Material - Shell	Steel
Net Weight	5.900/g
Number of Rows	1
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Flange
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-55° to +130°C
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20
Solder Process Data	
Lead-freeProcess Capability	N/A
Process Temperature max. C	130
Material Info	
Engineering Number	FM3W3S-K121
Reference - Drawing Numbers	
Sales Drawing	1727040032-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Missing Compliance Data	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
172704 Series
Mates With
FCT Mixed Layout D-Sub, Size 2, 3W3, Plug
Use With
FCT Coaxial, High Power, High Voltage, or Pneumatic Contacts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION