

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1727621002

Status:


Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Sigma Plug Housing, 4.20mm Pitch, Dual Row, UL 94V-0, Glow-Wire Capable, 2 Circuits



Documents:	
3D Model	Application Specification 2131370000-AS-000 (PDF)
3D Model (PDF)	Packaging Specification 1727620001-PK-000 (PDF)
Drawing (PDF)	Test Summary 2131370002-TS-000 (PDF)
Product Specification 2029880002-PS-000 (PDF)	Datasheet (PDF)
Product Specification 2131370000-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	172762
Application	Power, Wire-to-Board, Wire-to-Wire
Overview	Mini-Fit Family Power Connectors
Product Name	Mini-Fit Sigma
Taxonomy	Connector Housings
UPC	193264446148
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.100/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	2131370000-AS-000
Packaging Specification	1727620001-PK-000
Product Specification	2029880002-PS-000, 2131370000-PS-000
Sales Drawing	1727620001-SD-000
Test Summary	2131370002-TS-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

172762 Series

Mates With

Mini-Fit Sigma Receptacle Housing

1727081002

Use With

Mini-Fit TPA2/Sigma Male Terminal

172765 , 203070 . Mini-Fit Sigma Retainer

1727092001

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION