

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731100005

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Standard-Density Waterproof D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Plastic Watertight Frame, 9 Circuits, Red Insulator



Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General	
Product Family	D-Sub Products
Series	173110
IP Rating	IP67
Overview	FCT D-Sub Connectors
Product Category	D-Sub Connector
Product Name	FCT Products
Taxonomy	D-Sub Connectors
Type	Standard Density
UPC	889056319133
Physical	
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Red
Durability (mating cycles max)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Resin	PBT
Material - Shell	Brass
Net Weight	10.300/g
Number of Rows	2
Orientation	Straight
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel
Plating - Shell	Tin
Polarized to Mating Part	Yes
Ports	1
Shielded	Yes
Temperature Range - Operating	-25° to +70°C
Termination Style	Solder Cup
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67
Wire Size AWG	20
Electrical	
Current - Maximum per Contact	7.5A
Material Info	
Engineering Number	FWDR09S

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

173110 Series

Mates With

FCT Standard Density D-Sub, Size 1, 9 Position, Plug

Use With

FCT D-Sub Dust Caps

This document was generated on 01/02/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION