

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1731100004

Status:

Active

Overview:

FCT D-Sub Connectors

Description:

FCT Standard-Density Waterproof D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Plastic Watertight Frame, 9 Circuits, Red Insulator

Documents:

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General

Product Family

D-Sub Products

Series

173110

IP Rating

IP67

Overview

FCT D-Sub Connectors

Product Category

D-Sub Connector

Product Name

FCT Products

Taxonomy

D-Sub Connectors

Type

Standard Density

UPC

889056319126

Physical

Circuits (Loaded)

9

Circuits (maximum)

9

Color - Resin

Red

Durability (mating cycles max)

500

Gender

Male

Material - Contact

Copper Alloy

Material - Resin

PBT

Material - Shell

Brass

Net Weight

9.800/g

Number of Rows

2

Orientation

Straight

PCB Locator

No

PCB Retention

None

Packaging Type

Carton

Panel Mount

Rear

Panel Mount Method

Thread-In

Pitch - Mating Interface

2.84mm

Pitch - Termination Interface

2.84mm

Plating - Contact

Gold over Nickel

Plating - Shell

Tin

Polarized to Mating Part

Yes

Ports

1

Shielded

Yes

Temperature Range - Operating

-25° to +70°C

Termination Style

Solder Cup

Waterproof / Dustproof

Yes

Waterproof / Dustproof Type

IP67

Wire Size AWG

20

Electrical

Current - Maximum per Contact

7.5A

Material Info

Engineering Number

FWDR09P



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

173110 Series

Mates With

FCT Standard Density D-Sub, Size 1, 9 Position, Socket

Use With

FCT D-Sub Dust Caps

This document was generated on 01/09/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION