

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313721000

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Hybrid Receptacle Assembly, 10 Circuit, Black, Polarization A, without CPA



Series image - Reference only

|                                                                     |                                                                  |
|---------------------------------------------------------------------|------------------------------------------------------------------|
| Documents:                                                          |                                                                  |
| <a href="#">3D Model</a>                                            | <a href="#">Application Specification AS-31372-100-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                                       | <a href="#">Application Specification AS-34729-020-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                                      | <a href="#">Packaging Specification PK-31300-931-001 (PDF)</a>   |
| <a href="#">Product Specification PS-31372-100-001 (PDF)</a>        | <a href="#">Brochure (PDF)</a>                                   |
| <a href="#">Application Specification 347290200-AS-CH-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>             |

|                               |                                                                      |
|-------------------------------|----------------------------------------------------------------------|
| General                       |                                                                      |
| Product Family                | Crimp Housings                                                       |
| Series                        | 31372                                                                |
| Application                   | Automotive, Power, Wire-to-Board                                     |
| Comments                      | Polarization A, 6 x 1.50 and 4 x 2.8                                 |
| Overview                      | <a href="#">Stac64 Single, Multi-Pocket and Hybrid Header System</a> |
| Product Name                  | Stac64                                                               |
| Taxonomy                      | Connector Housings                                                   |
| UPC                           | 822348054497                                                         |
| Physical                      |                                                                      |
| Circuits (maximum)            | 10                                                                   |
| Color - Resin                 | Black                                                                |
| Gender                        | Receptacle                                                           |
| Glow-Wire Capable             | No                                                                   |
| Keying to Mating Part         | None                                                                 |
| Lock to Mating Part           | Yes                                                                  |
| Material - Resin              | Modified Polystyrene                                                 |
| Net Weight                    | 8.060/g                                                              |
| Number of Rows                | 2                                                                    |
| Packaging Type                | Partitioned Carton                                                   |
| Panel Mount                   | No                                                                   |
| Pitch - Mating Interface      | 3.50mm, 5.25mm                                                       |
| Polarized to Mating Part      | Yes                                                                  |
| Stackable                     | No                                                                   |
| Temperature Range - Operating | -40° to +100°C                                                       |
| Electrical                    |                                                                      |
| Current - Maximum per Contact | 22.0A, 30.0A                                                         |
| Solder Process Data           |                                                                      |
| Lead-freeProcess Capability   | N/A                                                                  |
| Material Info                 |                                                                      |
| Reference - Drawing Numbers   |                                                                      |
| Application Specification     | 347290200-AS-CH-000, AS-31372-100-001, AS-34729-020-001              |
| Packaging Specification       | PK-31300-931-001                                                     |
| Product Specification         | PS-31372-100-001                                                     |
| Sales Drawing                 | 313729000-000                                                        |

EU ELV  
Compliant

EU RoHS  
Compliant

REACH SVHC  
Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

Halogen-Free  
Status  
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV  
Compliant

RoHS Phthalates  
Not Contained

Search Parts in this Series  
[31372](#) Series

Mates With  
Stac64 Right Angle Assembly [34696](#) .  
Stac64 Vertical Assembly [34695](#)

Use With  
MX150 Terminal [33012](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**