

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0310681010

Status:


Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm H-DAC 64, 4 Way Receptacle Assembly, Single Row, Polarization A



Documents:	
3D Model (PDF)	Application Specification AS-31067-100-001 (PDF)
3D Model	Packaging Specification PK-30907-737-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-076-001 (PDF)
Product Specification PS-31100-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31068
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option A, Black
Overview	H-DAC 64 Unsealed Connector System
Product Name	H-DAC 64
Taxonomy	Connector Housings
UPC	800756062952
Physical	
Circuits (maximum)	4
Color - Resin	Black, White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.385/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	11.0A, 9.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-31067-100-001
Packaging Specification	PK-30907-737-001, PK-31301-076-001
Product Specification	PS-31100-0001-001
Sales Drawing	SD-31109-003-001

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image
Compliant

Not Contained

Search Parts in this Series
31068 Series

Mates With
HDAC 64, 4 Way Male Housing Assembly
310681040 , 310681070 , 311000040 ,
311010040

Use With
See Product Specification