

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0347290120
Status:	Active
Overview:	
Description:	Stac64 Receptacle Housing, 12 Circuits, Dual Row, Polarization A, Black, Tray
General Product Family Series Application Overview Polarization Product Name Taxonomy UPC Crimp Housings 34729 Automotive, Signal, Wire-to-Board stac64_single_multipocket_and_hybrid_header_system A Stac64 Connector Housings 884982006614	
Physical Circuits (maximum) Color - Resin Gender Glow-Wire Capable Keying to Mating Part Lock to Mating Part Material - Resin Net Weight Number of Rows Packaging Type Panel Mount Pitch - Mating Interface Pitch - Termination Interface Polarized to Mating Part Stackable Temperature Range - Operating 12 Black Receptacle No None Yes High Temperature Thermoplastic 5.300/g 2 Tray N/A 2.54mm 2.54mm Yes Yes -40° to +100°C	
Electrical Current - Maximum per Contact 10.0A	
Solder Process Data Lead-freeProcess Capability N/A	
Material Info	
Reference - Drawing Numbers Application Specification Packaging Specification Product Specification Sales Drawing 347290200-AS-CH-000, AS-34729-020-001 PK-31301-201-001 PS-34729-020-001 SD-34729-020-001	

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34729 Series

Mates With

34690 2.54mm Pitch Stac64 Vertical Header, 34691 2.54mm Pitch Stac64 Right Angle Header

Use With

34803 CTX64 Female Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION