

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0050842040

Status:

Active

Overview:

MLX Power Connectors

Description:

2.13mm Diameter MLX Pin and Socket Receptacle, 4 Circuits, Natural

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-42022-0001-001 (PDF)

Packaging Specification PK-42022-XX-001 (PDF)

Test Summary TS-42022-0001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	42022
Application	Power, Wire-to-Wire
Comments	Glow Wire Equivalent Part Number 366440004; Maximum current per contact 20A if used with 36663 and 36664 terminal
Overview	MLX Power Connectors
Product Name	MLX
Taxonomy	Connector Housings
UPC	800753754690
Physical	
Circuits (maximum)	4
Circuits Detail	4
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	3.955/g
Number of Rows	1
Packaging Type	Carton
Panel Mount	Yes
Pitch - Mating Interface	6.35mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-55° to +105°C
Electrical	
Current - Maximum per Contact	20.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	42022-4A
Reference - Drawing Numbers	
Packaging Specification	PK-42022-XX-001
Product Specification	PS-42022-0001-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

42022 Series

Mates With

MLX Power Crimp Housing Plug 42021

Use With

MLX Crimp Terminal 42023 , 42024 . MLX Male Pre-Crimped Lead 797582029 , 797582030 . MLX Female Pre-Crimped Lead 797582031 , 797582032

This document was generated on 01/05/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION