

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0533750410

Status:

Active

Overview:

Mini-Lock Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-Lock PCB Header, Single Row, Vertical, Through Hole with Kinked Pins, Tin Plating, Positive Lock, 4 Circuits, Bag, 3.40mm PC Tail Length

Documents:

- [Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[3D Model](#)

[Product Specification 511630000-PS-000 \(PDF\)](#)

[Product Specification 511631000-PS-000 \(PDF\)](#)

[Product Specification PS-51103-005-001 \(PDF\)](#)
- [Packaging Specification 533759200-SPK-200 \(PDF\)](#)

[Packaging Specification SPK-53375-001-001 \(PDF\)](#)

[Packaging Specification SPK-53375-001-002 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	53375
Application	Signal, Wire-to-Board
Component Type	PCB Header
Overview	Mini-Lock Wire-to-Board Connector System
Product Name	Mini-Lock
Taxonomy	PCB Headers and Receptacles
UPC	800753632974

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	563.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.40mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-55° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

53375 Series

Mates With

Mini-Lock Receptacle [51163](#) . Mini-Lock
Cable Assembly [15137](#)

Termination Interface: Style	Through Hole - Kinked Pin
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	533759200-SPK-200, SPK-53375-001-001, SPK-53375-001-002
Product Specification	511630000-PS-000, 511631000-PS-000, PS-51103-005-001
Sales Drawing	533750000-SD-000

This document was generated on 01/16/2023

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION