

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5600850101

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik Crimp Terminal, Female, 22-26 AWG, Reel

Documents:

Drawing (PDF)

Product Specification PS-502351-001-001 (PDF)

Application Specification AS-560085-001-JP-001 (PDF)

Packaging Specification PK-560085-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

|                                |                                          |
|--------------------------------|------------------------------------------|
| General                        |                                          |
| Product Family                 | Crimp Terminals                          |
| Series                         | 560085                                   |
| Application                    | Automotive, Power, Signal, Wire-to-Board |
| Crimp Quality Equipment        | Yes                                      |
| Overview                       | DuraClik Connector System                |
| Product Name                   | DuraClik                                 |
| Taxonomy                       | Crimp Terminals                          |
| UPC                            | 887191151892                             |
| Physical                       |                                          |
| Gender                         | Female                                   |
| Material - Metal               | Phosphor Bronze                          |
| Material - Plating Mating      | Tin                                      |
| Material - Plating Termination | Tin                                      |
| Net Weight                     | 0.049/g                                  |
| Packaging Type                 | Reel                                     |
| Termination Interface: Style   | Crimp or Compression                     |
| Wire Insulation Diameter       | 1.40mm                                   |
| Wire Size AWG                  | 22, 24, 26                               |
| Wire Size mm²                  | 0.34                                     |
| Electrical                     |                                          |
| Voltage - Maximum              | 125V                                     |
| Solder Process Data            |                                          |
| Lead-freeProcess Capability    | N/A                                      |

Material Info

|                               |                                      |
|-------------------------------|--------------------------------------|
| Reference - Drawing Numbers   |                                      |
| Application Specification     | AS-560085-001-JP-001                 |
| Application Tooling Documents | 571753710ATS-000, 571753710ATS-J-000 |
| Packaging Specification       | PK-560085-001-001                    |
| Product Specification         | PS-502351-001-001                    |
| Sales Drawing                 | SD-560085-001-001                    |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series  
560085 Series

Use With  
502351 DuraClik Wire-to-Board Receptacle Housing

|                                                                                                                                                                                 |            |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|
| Application Tooling   <a href="#">FAQ</a>                                                                                                                                       |            |
| Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document. |            |
| Global                                                                                                                                                                          |            |
| Description                                                                                                                                                                     | Product #  |
| Extraction Tool for Micro-Fit Terminals                                                                                                                                         | 11030043   |
| FineAdjust Applicator for 2.0 Wire-to-Board Crimp Receptacle Terminal and SMEC Crimp Receptacle Terminals, 22-26 AWG and AVSS 0.3 Wires                                         | 2037021900 |

PremiumGrade Hand638235100  
Crimp Tool for Micro-  
Latch, DuraClik, and  
Servo Motor Encoder  
Female Terminals,  
22-26 AWG

This document was generated on 10/20/2022  
**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**