

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5601230400

Status:

Active

Overview:

DuraClik Connector System

Description:

DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 4 Circuits

- Documents:
- Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-560123-001-001 (PDF)

Product Specification PS-560123-003-001 (PDF)

Application Specification AS-560123-001-001 (PDF)

Packaging Specification PK-560123-001-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

Taxonomy

UPC

Crimp Housings

560123

Automotive, Signal, Wire-to-Board

DuraClik Connector System

DuraClik

Connector Housings

887191705538

Physical

Circuits (maximum)

Color - Resin

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

4

White

Receptacle

No

None

Yes

PBT

0.274/g

1

Bag

No

2.00mm

Yes

No

-40° to +130°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

AS-560123-001-001

PK-560123-001-001

PS-560123-001-001, PS-560123-003-001

SD-560123-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

560123 Series

Mates With

DuraClik Right-Angle Header 502352

DuraClik Vertical Header 560020

Use With

DuraClik ISL Terminal 560124

DuraClik ISL Retainer 5601250400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION