

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0731010120

Status:

Active

Overview:

Description:

75 Ohms, BNC Right-Angle PCB Bulkhead Jack Receptacle with Board Locks, Low Profile, Tray

|                                                |                             |
|------------------------------------------------|-----------------------------|
| Agency Certification                           |                             |
| UL                                             | E107635                     |
| General                                        |                             |
| Product Family                                 | RF/Coax Connectors          |
| Series                                         | 73101                       |
| Comments                                       | Low Profile                 |
| Overview                                       | bnc                         |
| Product Name                                   | BNC                         |
| Style                                          | PCB                         |
| Taxonomy                                       | RF / Coaxial Connectors     |
| Type                                           | Miniature                   |
| UPC                                            | 800753680296                |
| Wire/Cable Type                                | N/A                         |
| Physical                                       |                             |
| Flammability                                   | 94V-2                       |
| Gender                                         | Jack                        |
| Keying to Mating Part                          | None                        |
| Net Weight                                     | 16.575/g                    |
| Orientation                                    | Right Angle                 |
| PCB Mounting                                   | Through Hole                |
| PCB Thickness - Recommended                    | 3.20mm                      |
| Packaging Type                                 | Tray                        |
| Panel Mount                                    | Yes                         |
| Panel Mount Method                             | Bulkhead                    |
| Reverse Polar                                  | No                          |
| Electrical                                     |                             |
| Frequency                                      | 2 GHz                       |
| Impedance                                      | 75Ω                         |
| Power / Voltage                                | VOLTAGE: 500 Vrms@Sea Level |
| Solder Process Data                            |                             |
| Duration at Max. Process Temperature (seconds) | 005                         |
| Lead-freeProcess Capability                    | WAVE                        |
| Max. Cycles at Max. Process Temperature        | 001                         |
| Process Temperature max. C                     | 245                         |
| Material Info                                  |                             |
| Reference - Drawing Numbers                    |                             |
| Sales Drawing                                  | SD-73101-0120-001           |

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

73101 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION